

High Speed Adapter Kit 高速轉板套件

For LAP-C Pro



新北市中和區建八路123號2樓
2F., No.123, Jian 8th Rd., Zhonghe Dist.,
New Taipei City 23585, Taiwan

台北業務部 ☎ +886 2-6620-2225 #200
✉ service@zeroplus.com.tw

Sales Dep ☎ +886 2-6620-2225 #380
(Japanese service line #242)

✉ sales@zeroplus.com.tw

🌐 www.zeroplus.com.tw




ZEROPUS



f ZP FB

Copyright © ZEROPLUS TECHNOLOGY CO., LTD. All Rights Reserved.

ver.2004



Brief Introduction



- 16 + 2 channels shielding logic probe for satisfying high frequency measurement
16 + 2 通道屏蔽邏輯探頭，滿足高頻量測情境。

- Provide high sample rate up to 2GS/s
(For LAP-C Pro 32 channels series)
可提供訊號取樣率高達2GS/s
(針對LAP-C Pro 32 通道系列機種)。

- Each cable is with Signal wire (color) and GND wire (black)
每組訊號線 (彩色) 均搭配一條地線GND (黑色)。

- Reduce noise for clarifying signal
減少雜訊干擾，讓量測訊號更佳清晰。

Pin	Name	Pin	Name
1	A0	2	A1
3	A2	4	A3
5	GND	6	A4
7	A5	8	A6
9	A7	10	CK0
11	B0	12	B1
13	B2	14	B3
15	GND	16	B4
17	B5	18	B6
19	B7	20	CK1




Step 1: Please assemble 2 wires to corresponding ports.

請將兩組測試線，連接至高速轉板的兩個連接埠。

< A0> A0 & A1> A1; both colored stickers on wires face outside >

< A0> A0 & A1> A1; 依照測試線與轉板上，相同的序號連接，貼紙均朝向外側>



Step 2: Please insert High Speed Adapter Kit to LAP-C Pro series.

請將高速轉板套件，連接至LAP-C Pro系列機種。

< A0> A0 & A1> A1; both colored stickers on wires face outside >

< A0> A0 & A1> A1; 依照高速轉板套件與LAP-C Pro上，相同的貼紙連接，貼紙均朝向外側>

